

Great Display and Mobility FingerTec Flexi Kit



FingerTec Time Attendance products are best fixed on a wall with the wiring concealed neatly.

However, for users who are hesitant to hack the wall and prefer to have the terminals on tabletop without much hassle of installation, FingerTec introduces our very own Flexi Kit, an accessory especially designed to fix the terminals on.

The FingerTec Flexi Kit comes as a foldable unit, easy to setup when needed, can be neatly packed away in a lockable cupboard and it is convenient to carry about. The material for the flexi kit is light yet robust, handy and sophisticated.

FingerTec Flexi Kit is best used for:

- A great prop for demonstration, exhibition and display
- Attendance on reception table
- Mobile units for attendance on sites

INSTALLATION GUIDE



1. Get the flexi kit ready.
2. Place the terminal back plate on the flexi kit, and screw it onto the designated areas.
3. Attach the terminal to the corresponding back plate.
4. Tighten the screw at the bottom of the terminal to secure the terminal on the flexi kit.

SPECIFICATIONS

MATERIAL	Polycarbonate
DIMENSION (MM)	255 (L) x 5 (W) x 235 (H) (Folded)
	255 (L) x 178 (W) x 235 (H) (Opened)
WEIGHT	0.6 kg

